
# WIREMOLD

## V500<sup>®</sup>/V700<sup>®</sup>/700WH Steel Raceway

### 

## **One-Piece Surface Steel Raceway**

deal for surface mounting small amounts of electrical wiring or communication cables. These rugged raceways offer a low profile appearance which blend with any decor. V500, V700, and 700WH come in our exclusive ScuffCoat<sup>™</sup> finish.



V500 and V700.



5700 Series boxes with Pass & Seymour Activate inserts.

#### Features & Benefits


- Low-profile, unobtrusive appearance. Blends with any decor or setting. Excellent for low-voltage wiring.
- ScuffCoat finish. Tough, durable, scratch-resistant finish which can be overpainted with latex paint.
- Surface mounting. Eliminates disturbing the building structure or wall finish to make renovations easy.



- V5748-3Device Box accommodates wireless. Designed for use with Ortronics<sup>®</sup> Wi-Jack<sup>™</sup> Wireless Access Points.
- **Full line of fittings.** Provides unlimited wiring solutions and interconnection between raceway systems.
- More choice of colors. 700 Series Raceway and Fittings are available in ivory and white.

- **Fittings have removable covers.** Allows easy access to wiring for changes and additions.
- Raceway cutters with replaceable blades. Cuts raceway cleanly, reduces labor, and installation time.
- Datacom connectivity options. Accepts industry standard and proprietary devices from a wide range of manufacturers to provide a seamless and aesthetically pleasing interface for voice, data, audio, and video applications at the point of use.
- UL5 and ADA compliant. Raceway and fittings meet UL5 specifications and can be installed in conformance with ADA requirements.

### V500 & 700 Series System Product Applications



• · · · · ·	V500, V700, & 700W		
Catalog No./Item	Description/Specifications	Catalog No./Item	Description/Specifications
V500 17/32" [13.5mm] 3/4"	<b>Raceway</b> – .040" [1.0mm] steel. Comes in 10 ft. [3.05mm] lengths, one 5701 Coupling furnished with each length. Five ft. [1.525m] lengths available, order V500-5.	V506 V706 706 WH	Connection Cover – To cover openings where lengths of V500 or 700 Series, not squarely cut, come together.
[19.1mm]		V511	90° Flat Elbow – For right angle
V700 700 WH 21/32" [16.7mm] 3/4"	Raceway – .040" [1.0mm] steel. Comes in 10 ft. [3.05mm] lengths, one 5701 Coupling furnished with each length. Five ft. [1.525m] lengths available, order V700-5.	V711 711WH	turns on same surface.
[19.1mm]		V512	45° Flat Elbow – For diagonal 45
502 702	<b>Bushing</b> – Protects wires from abrasion. Bushing slips into open end of raceway where it enters a fitting.	V712 11/4" [32mm]	turns on same surface.
V504	Mounting Strap (1- or 2-Hole) –	3/4" [19.1mm]	
V704 704WH	Convert to one-hole by breaking off at score. Lanced tab holds strap in place while fastening to surface.   CAT. # A B   V504 1 7/8" [47mm] 1/2" [12.7mm]   V704 1 7/8" [47mm] 5/8" [15.4mm]	V517 V717 2 3/4" 717WH [70mm]	Internal Elbow – For inside surfaces at right angles.

NOTE: Use #6 flat head screws with all fittings requiring screws except V504/V704, and V57200 Series; with V504/V704 use #8 pan head screws; with V57200 Series use #8 flat head screws.