Sta-Kon[®] Terminal Products and Tools

Nylon-Insulated Fork Terminals

- Fork terminals enable easy installation because the mounting screw does not have to be completely removed
- Brazed seam barrel is serrated for high pull-out value. Terminal is high conductivity electrolytic copper, electrotin plated. Insulation is color-coded
- Vinyl insulated fork terminals have extra-long PVC insulation sleeve for protection and stress relief at wire's flex point
- Suffix "X" indicates an expanded insulation support, meaning a wider wire entry to accommodate heavy wall insulation



Nylon-Insulated Fork
PKG, WIRE MAX, BOLT BEC, DIMENSIONS STOCK

	PKG.	WIRE	MAX.	BOLT	REC.		DIME	NSION	S	STOCK
CAT. NO.	QTY.	RANGE	INS.	HOLE	TOOL	Α	В	C	М	THICK.
RA18-6F	100	22–16	.136	#6		.83	.25	.25	.71	
RA1103	1,000	22–16	.136	#6		.83	.25	.25	.71	
RA18-8F	100	22–16	.136	#8		.86	.31	.25	.71	
RA1123	1,000	22–16	.136	#8		.86	.31	.25	.71	
RA18-10F	100	22–16	.136	#10		.86	.31	.25	.71	.02
RA1153	1,000	22–16	.136	#10		.86	.31	.25	.71	
RA18-14F	100	22–16	.136	1/4"		.95	.44	.31	.70	
RA1163	1,000	22–16	.136	1/4"		.95	.44	.31	.70	
RB14-6F	100	18–14	.162	#6		.87	.31	.25	.71	
RB1113	1,000	18–14	.162	#6		.87	.31	.25	.71	
RB14-8F	100	18–14	.162	#8		.87	.31	.25	.71	
RB1123	1,000	18–14	.162	#8		.87	.31	.25	.71	
RB14-10F	100	18–14	.162	#10		.87	.38	.25	.71	
RB1153	1,000	18–14	.162	#10	ERG	.87	.38	.25	.71	.03
RB14-14F	100	18–14	.162	1/4"	2001	.95	.44	.28	.74	
RB1163	1,000	18–14	.162	1/4"	2001	.95	.44	.28	.74	
RB1103	1,000	18–14	.162	#6		.74	.28	.16	.60	
RB1124	1,000	18–14	.190	#8		.95	.31	.25	.79	
RB1154	1,000	18–14	.190	#10		.95	.31	.25	.79	
RC10-6F	50	12–10	.210	#6		.97	.31	.27	.81	
RC1113	500	12–10	.210	#6		.97	.31	.27	.81	
RC10-8F	50	12–10	.210	#8		1.00	.37	.27	.81	
RC1123	500	12–10	.210	#8		1.00	.37	.27	.81	
RC10-10F	50	12–10	.210	#10		1.00	.37	.27	.81	
RC1153	500	12–10	.210	#10		1.00	.37	.27	.81	.04
RC10-14F	50	12–10	.210	1/4"		1.12	.50	.27	.86	
RC1163	500	12–10	.210	1/4"		1.12	.50	.27	.86	
RC1124	1,000	12–10	.250	#8		1.10	.37	.27	.91	
RC1154	1,000	12–10	.250	#10		1.10	.37	.27	.91	

Nylon-Insulated Locking Fork

	e		~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~			
Q			2	S	ى لار	Ð
PKG	WIRE	MAX	BOLT	REC	DIMENSIONS	STOCK

	PKG.	WIRE	MAX.	BOLT	REC.	DIMENSIONS				STOCK
CAT. NO.	QTY.	RANGE	INS.	HOLE	TOOL	Α	В	C	М	THICK.
RA18-6FL	100	22–16	.136	#6		.86	.25	.25	.71	
RA2213	1,000	22–16	.136	#6		.86	.25	.25	.71	
RA18-8FL	100	22–16	.136	#8		.86	.29	.25	.71	
RA2243	1,000	22–16	.136	#8		.86	.29	.25	.71	.02
RA18-10FL	100	22–16	.136	#10		.86	.29	.25	.71	
RA2253	1,000	22–16	.136	#10		.86	.29	.25	.71	
RB14-6FL	100	18–14	.162	#6		.87	.25	.25	.71	
RB2213	1,000	18–14	.162	#6		.87	.25	.25	.71	
RB2214	1,000	18–14	.190	#6		.95	.25	.25	.79	
RB14-8FL	100	18–14	.162	#8		.87	.29	.25	.71	
RB2233	1,000	18–14	.162	#8		.87	.29	.25	.71	.03
RB14-10FL	100	18–14	.162	#10	ERG	.87	.29	.25	.71	
RB2253	1,000	18–14	.162	#10	2001	.87	.29	.25	.71	
RB2254	1,000	18–14	.190	#10		.95	.29	.25	.71	
RC10-6FL	50	12–10	.210	#6		.97	.31	.27	.81	
RC2203	500	12–10	.210	#6		.97	.31	.27	.81	
RC2204	1,000	12–10	.250	#6		1.07	.31	.27	.91	
RC10-8FL	50	12–10	.210	#8		1.00	.37	.27	.81	
RC2213	500	12–10	.210	#8		1.00	.37	.27	.81	
RC10-10FL	50	12–10	.210	#10		1.00	.37	.27	.81	.04
RC2223	500	12–10	.210	#10		1.00	.37	.27	.81	
RC2224	1,000	12–10	.250	#10		1.10	.37	.27	.91	
RC10-14FL	50	12–10	.210	1⁄4"		1.12	.50	.32	.86	
RC2233	500	12–10	.210	1/4"		1.12	.50	.32	.86	

Thomas®Betts

www.tnb.com

Tel: 901.252.8000 800.816.7809 Fax: 901.252.1354

United States

Canada Tel: 450.347.5318 Fax: 450.347.1976 Technical Services Tel: 888.862.3289