



Actual

Catalog Number: RD8-14
Product ID: 7TAI029820R0048
UPC Number: 78621087202
EAN Number: 05414363159759
Status: Active

Nylon Insulated Large Ring Terminal, Length 1.48 Inches, Width .42 Inches, Maximum Insulation .340, Bolt Hole #10, Wire Range 8, Color Red, Copper, Tin Plated

- Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.
- Application Tools: ERG4007
- Alternate Package Qty: RD717

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ring Terminal
Special Features	Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.
Standard	UL E9809
Wire Size	8
Voltage Rating	600V
Material	Copper
Color	Red

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	PA
Colour insulation	Red
Reel packaging	N
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	25
Inner Dimensions (inches)	2.5x1.3x3.5
Outer Quantity	250
Outer Dimensions (inches)	11.5x9.5x7.5
Weight Uom	1.25 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com