



Actual

Catalog Number: NC301
Product ID: 7TAA010050R0002
UPC Number: 78599142751
EAN Number: 05414363155973
Status: Active

Connector, Clamp-Type, Conduit Size 3/8 Inch, Clamping Range 0.18 Inch - 0.64 Inch, Width 1.16 Inch, Die Cast Zinc

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Steel City
Type	Clamp Type Connectors
Application	For use with non-metallic sheathed cable
Standard	UL e17583
Size	3/8
Material	Zinc Die Cast

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/8 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
One-piece	Y
Material housing	Zinc die-cast
Surface protection	Untreated
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit FI	N

Packaging

Inner Quantity	100
Inner Dimensions (inches)	7.813x4.25x4
Outer Quantity	1000
Outer Dimensions (inches)	20.3x9.5x8.7
Weight Uom	5.56 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com