



Actual

**Catalog Number:** NC302  
**Product ID:** 7TAA010050R0003  
**UPC Number:** 78599142753  
**EAN Number:** 05414363155980  
**Status:** Active

Connector, Clamp-Type, Conduit Size 3/4 Inch, Clamping Range 0.41 Inch - 0.82 Inch, Width 1.87 Inch, Die Cast Zinc

### North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Steel City
Type	Clamp Type Connectors
Application	For use with non-metallic sheathed cable
Standard	UL e17583
Size	3/4 Inch
Material	Zinc Die Cast

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/4 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
One-piece	Y
Material housing	Zinc die-cast
Surface protection	Untreated
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit FI	N

### Packaging

Inner Quantity	50
Inner Dimensions (inches)	7.5x5.5x3.75
Outer Quantity	500
Outer Dimensions (inches)	18.8x11.4x8.6
Weight Uom	12 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)