



Actual



Family

Catalog Number: CC-NPT-12-G-3
Product ID: 7TAD105070R0002
UPC Number: 78621091577
EAN Number: 05415022258165
Status: Active

Multi-Hole Cord Grip Connector with 3 Openings, 1/2 Inch Thread Length 0.590 Inch/15mm, Cable Range 0.190 to 0.250 Inch, Nylon, Gray

- Sturdy cable sealing mechanism which results in superior strain relief.
- Compact size ensures quick and easy installation in cramped spaces
- Non-metallic construction provides excellent corrosion, chemical and impact resistance.

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Multi-Hole Cord Connectors
Special Features	Sturdy Cable Sealing Mechanism Which Results In Superior Strain Relief
Application	Ideal for Connections and Strain Relief in Cramped Spaces
Standard	UL E13938
Size	1/2 Inch
Conductor Range	3 Openings, 0.190 to 0.250 Inch
Material	Nylon
Color	Gray
Temperature Rating	-30 to +80 Degrees C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Thread length	15.0mm
Suitable for cable diameter	4.826-6.35mm
Material	Plastic
Material quality	Polyamide (PA)
Colour	Light grey
Model	Straight
Operating temperature	-30-+80°C

Packaging

Inner Quantity	50
Inner Dimensions (inches)	4x4x3
Outer Quantity	250
Outer Dimensions (inches)	20.5x5.4x8.9
Weight Uom	4 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000375
Instruction Sheet 1	ta02021-tb2

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com