



Actual

Catalog Number: CSS-LH
Product ID: 7TAA159150R0000
UPC Number: 78621070172
EAN Number: 05414363149910
Status: Active

Deltec Cable Tie Locking Head Only, Black Acetal for Temperatures up to 85 Degrees Celsius (185 F), Length of 21.59mm (0.85 Inches), Width of 19.05mm (0.75 Inches), Height of 12.57mm (0.495 Inches), Weather and Ultraviolet Resistant, Bulk Pack

- Perfect for coaxial, fiber optic and all other communication and electrical conducting cables.
- Strap and body are weatherable acetal, offering superior resistance to sunlight, moisture and salt environments.
- Locking device is marine-grade corrosion-resistant copper alloy.
- Application Tools: WT3D

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Brand Name	Deltec
Type	Locking Heads
Special Features	Perfect for coaxial, fiber optic and all other communication and electrical conducting cables.
Application	Ideal solution for bundling in harsh outdoor environments.
Material	Weather Resistant Acetel
Color	Black
Tensile Strength	250 Pounds/1112 Newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	19.05mm
Length belt/tape/tie	21.59mm
Model	Internal toothing
Band closure	Double lock head
Material	Plastic
Material quality	Other
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N

Packaging

Inner Quantity	25
Outer Quantity	500
Outer Dimensions (inches)	9.5x6.5x5.5
Weight Uom	0.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US Available on Website

For further technical assistance, please contact us...

Memphis, TN 38125
www.tnb.com

8155 T&B Blvd.
Memphis, TN 38125

Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com