



Actual

Catalog Number: E6-14
Product ID: 7TAI029570R0006
UPC Number: 78621080358
EAN Number: 05414363150510
Status: Active

Non-Insulated Large Brazed Seam Ring Terminal, Length 1.13 Inches, Width .48 Inches, Bolt Hole 1/2 Inch, Wire Range #6 AWG, Copper, Tin Plated, 20 Pack

- These non-insulated ring terminals are made of electrolytic copper for high conductivity.
- They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
- Serrated barrel increases grip on wire.
- Application Tools: WT115A, TBM6, TBM6S, WT3185
- Alternate Package Qty: E71

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ring Terminal
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.
Standard	UL E9809
Wire Size	6
Voltage Rating	600V
Material	Copper
Color	Metallic

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	N
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	20
Inner Dimensions (inches)	4.6x3.3x3.3
Outer Quantity	100
Outer Dimensions (inches)	15x9.5x8.8
Weight Uom	1.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Memphis, TN 38125
www.tnb.com

8155 T&B Blvd.
Memphis, TN 38125

Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com