



Actual

**Catalog Number:** RE10721  
**Product ID:** 7TAI029860R0081  
**UPC Number:** 78621083040  
**EAN Number:** 05414363159858  
**Status:** Active

Nylon Insulated Large Ring Terminal, Length 1.70 Inches, Width .60 Inches, Maximum Insulation .315, Bolt Hole 5/16 Inch, Wire Range 6AN, Color Blue, Copper, Tin Plated

- Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.
- Application Tools: ERG4007

### North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ring Terminal
Special Features	Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.
Standard	UL E9809
Wire Size	6AN
Voltage Rating	600V
Material	Copper
Color	Blue

### European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	Other
Colour insulation	Blue
Reel packaging	N
Material	Copper
Surface protection	Tinned

### Packaging

Inner Quantity	200
Inner Dimensions (inches)	6.1x4.6x3.1
Outer Quantity	2000
Outer Dimensions (inches)	17x10x7
Weight Uom	13.13 lbs. per 1000

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000207

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)