



Actual



Representative

Catalog Number: 2671
Product ID: 7TAD105040R0000
UPC Number: 78621002671
EAN Number: 05414363140146
Status: Active

Liquidtight Cord Connector, 3/8 Inch, Straight, Cord Range 0.125 to 0.275 Inch, Meets Coast Guard CG293, Nylon, Black

- Segmented chuck provides high mechanical pullout performance, will not cut or damage cord jacket.
- Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC. Class I, Div 2; Class II, Div 1 & 2; Class III, Div 1 & 2; NEC 501-4(b), 502-4(a)(b), 503-3(a)(b)
- Meets Coast Guard CG293

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Cord Connectors-Straight
Special Features	Hand Tightens, No Tools Needed for Assembly
Application	To Connect Flexible Cord to a Box or Enclosure and Provide Adequate Strain Relief.
Standard	UL E13938, CSA
Size	3/8 Inch
Conductor Range	0.125 to 0.275 Inch
Material	Nylon
Color	Black
Temperature Rating	-34 to +105 Degrees C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/8 inch
Thread length	11.90mm
Suitable for cable diameter	3.175-6.985mm
Material	Plastic
Material quality	Polyamide (PA)
Colour	Black
Model	Straight
Operating temperature	-34-+105°C

Packaging

Inner Quantity	25
Inner Dimensions (inches)	6x4.5x3
Outer Quantity	250
Outer Dimensions (inches)	12.6x11x9.1
Weight Uom	2.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website
Instruction Sheet 1	ta01320-tb2

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com