



Actual

Catalog Number: 2D-8
Product ID: 7TAI029580R0001
UPC Number: 78621080010
EAN Number: 05415022255201
Status: Active

Non-Insulated Butt Splice, Length 0.99 Inch, Width 0.27 Inch, Wire Range 10-8 AWG, Copper, Tin Plated

- Application Tools: WT115A, TBM6, TBM6S
- Alternate Package Qty: DD102

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Sta-Kon
Type	Splice Connector
Standard	UL E9809
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Voltage Rating	600V
Temperature Rating	150 Degrees C

European Specifications (ETIM)

ETIM	EC001059 Crimp splices for copper conductor
AWG-range	10-8
Material	Copper
Surface protection	Tinned
Insulation	None

Packaging

Inner Quantity	25
Inner Dimensions (inches)	2.06x1.13x2.94
Outer Quantity	250
Outer Dimensions (inches)	10.5x9x7.2
Weight Uom	1.19 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com