



Actual

## ELCON

**Catalog Number:** 2B-14  
**Product ID:** 7TAI029570R0000  
**UPC Number:** 78621080004  
**EAN Number:** 05414363140443  
**Status:** Active

Non-Insulated Butt Splice, Length 0.63 Inch, Width 0.16 Inch, Wire Range 18-14 AWG, Copper, Tin Plated, 100 Pack

- Application Tools: WT110M, WT111M, WT112M, WT2000, ERG4002
- Alternate Package Qty: BB2

### North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Sta-Kon
Type	Splice Connector
Standard	UL E9809
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Voltage Rating	600V
Temperature Rating	150 Degrees C

### European Specifications (ETIM)

ETIM	EC001059 Crimp splices for copper conductor
AWG-range	18-14
Material	Copper
Surface protection	Tinned
Insulation	None

### Packaging

Inner Quantity	100
Inner Dimensions (inches)	2.63x1.63x3.5
Outer Quantity	500
Outer Dimensions (inches)	15.1x9.4x9
Weight Uom	15 lbs. per 1000

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)