



Actual

Catalog Number: LTC075GY
Product ID: 7TAD012610R0009
UPC Number: 78621088077
EAN Number: 05414363155126
Status: Active

Commercial Grade, Type B Liquidtight Flexible PVC Conduit, 3/4 Inch Conduit Size, Approved for Outdoor and Direct Burial in the US, UL Temperature Ratings - 80 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, Oil Resistant, Voltage Rating 600V, Gray

- Fast installation, even in tight or cramped spaces.
- Smooth inner diameter allows easy wire pulling.
- Smooth outer jacket uses material approved for outdoor use, is sunlight resistant and oil resistant.
- Lightweight and liquidtight.
- UL Listed for direct burial

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	T&B
Type	Liquidtight Flexible Non-Metallic Conduit
Special Features	The Smooth Inner Surface Ensures that Cables and Conductors Can Be Fed Through Very Easily
Application	Machine Tools, Motor Hookups, Food Processing Equipment, Extensions from Wire Ways, and Sensor and Micro Switch Wiring Found In Control Consoles.
Standard	UL E95745, CSA
Trade Size	3/4 Inch
Outside Diameter	26.7mm
Inside Diameter	20.8mm
Length	30.5 Meters
Voltage Rating	600 Volts
Material	PVC
Color	Gray

European Specifications (ETIM)

ETIM	EC001177 Protective plastic hose
Nominal size in inch	3/4 inch
Material	PVC
Operating temperature	-18-+105°C
Flexibility	Flexible
Colour	Grey
Approved according to CSA	Y

Packaging

Outer Quantity	100
Outer Dimensions (inches)	22.5x22.5x6.5
Weight Uom	19.38 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com