



Representative

**Catalog Number:** B14-8  
**Product ID:** 7TAI029580R0013  
**UPC Number:** 78621080320  
**EAN Number:** 05414363148463  
**Status:** Active

Non-Insulated Ring Terminal, Length .75 Inches, Width .31 Inches, Bolt Hole #8, Wire Range #18-#14 AWG, Copper, Tin Plated

- These non-insulated ring terminals are made of electrolytic copper for high conductivity.
- They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
- Serrated barrel increases grip on wire.
- Application Tools: WT110M, WT111M, WT112M, WT2000, ERG4002
- Alternate Package Qty: B86

### North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ring Terminal
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.
Standard	UL E9809
Wire Size	18-14
Voltage Rating	600V
Material	Copper
Color	Metallic

### European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	N
AWG-range	18-14
Material	Copper
Surface protection	Tinned

### Packaging

Inner Quantity	100
Inner Dimensions (inches)	2.63x1.63x3.5
Outer Quantity	500
Outer Dimensions (inches)	15x9.4x8.7
Weight Uom	2.5 lbs. per 1000

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)