



Actual

Catalog Number: RA1147
Product ID: 7TAI029500R0000
UPC Number: 78621081761
EAN Number: 05414363157403
Status: Active

Vinyl Insulated Fork Terminal, Length .97 Inches, Width .31 Inches, Maximum Insulation .150, Bolt Hole #8, Wire Range #22-#16 AWG, Color Red, Copper, Tin Plated

- These fork terminals have extra-long PVC insulation sleeve for protection and stress relief at wire's flex point.
- Brazed seam barrel is serrated for high pull-out value.
- Insulation is color-coded.
- Application Tools: WT145C, WT2000, WT112M, ERG4001
- Alternate Package Qty: 18RA-8F

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Fork Terminal
Special Features	These fork terminals have extra-long PVC insulation sleeve for protection and stress relief at wires flex point. Brazed seam barrel is serrated for high pull-out value. Insulation is color-coded.
Standard	UL E9809
Wire Size	22-16
Voltage Rating	600V
Material	Copper
Color	Red

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Fork shape
Insulation	PVC
Colour insulation	Red
Reel packaging	N
AWG-range	22-16
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	6.1x4.6x3.1
Outer Quantity	10000
Outer Dimensions (inches)	16.7x10.2x6.7
Weight Uom	2.5 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Memphis, TN 38125
www.tnb.com

8155 T&B Blvd.
Memphis, TN 38125

Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com