



Actual



Actual

Catalog Number: 10RC-14
Product ID: 7TAI029450R0003
UPC Number: 78621080046
EAN Number: 05414363136224
Status: Active

Vinyl-Insulated Ring Terminal, Length 1.16 Inches, Width .50 Inches, Maximum Insulation .210, Bolt Hole 1/4 Inch, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated

- These terminals are self-insulated with a PVC insulation sleeve of extra length to give protection and relieve bending stress at wire's flex point.
- Brazed seam barrel is serrated to obtain high pull-out value.
- Application Tools: WT145C, WT2000, WT112M, ERG4001
- Alternate Package Qty: RC717

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ring Terminal
Special Features	These terminals are self-insulated with a PVC insulation sleeve of extra length to give protection and relieve bending stress at wires flex point. Brazed seam barrel is serrated to obtain high pull-out value.
Standard	UL E9809
Wire Size	12-10
Voltage Rating	600V
Material	Copper
Color	Yellow

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	PVC
Colour insulation	Yellow
Reel packaging	N
AWG-range	12-10
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	50
Outer Quantity	250
Outer Dimensions (inches)	12.1x10.3x8.1
Weight Uom	6.25 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com