



Actual

**Catalog Number:** TC5141  
**Product ID:** 7TAG009870R0002  
**UPC Number:** 78621087357  
**EAN Number:** 05414363058823  
**Status:** Active

Saddle Support Mounting Base, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length of 17.07mm (0.672 Inches), Width of 11.13mm (0.438 Inches), Height of 8.33mm (0.0.328 Inches), Mount with #6 Screw, 100 Pack

- This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.

### North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Brand Name	Ty-Rap
Type	Saddle Support Base
Special Features	This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.
Mount Size	#6
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 Degree F to 185 Degree F

### European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	17.07mm
Width	11.13mm
Height	8.33mm
Suitable for cable tie width to	4.8mm
Type of fastening	Other
Diameter mounting hole	3.8mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

### Packaging

Inner Quantity	100
Outer Quantity	500
Outer Dimensions (inches)	9.8x6.4x4
Weight Uom	2.5 lbs. per 1000

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)