



Actual

Catalog Number: TC141
Product ID: 7TAG009880R0006
UPC Number: 78621082272
EAN Number: 05414363058205
Status: Active

Saddle Support Mounting Base, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length of 17.07mm (0.672 Inches), Width of 11.13mm (0.438 Inches), Height of 8.33mm (0.328 Inches), Screw Mounting Method, #6 Pan Head Screw, Bulk Pack

- This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Brand Name	Ty-Rap
Type	Saddle Support Base
Special Features	This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.
Mount Size	#6
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 Degree F to 185 Degree F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	17.07mm
Width	11.13mm
Height	8.33mm
Suitable for cable tie width to	2.4mm
Type of fastening	Other
Diameter mounting hole	3mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

Packaging

Inner Quantity	500
Inner Dimensions (inches)	15x12x3
Outer Quantity	5000
Outer Dimensions (inches)	16.5x8.95x7.5
Weight Uom	1.88 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321

