



Actual

**Catalog Number:** TC102  
**Product ID:** 7TAG009880R0001  
**UPC Number:** 78621082242  
**EAN Number:** 05414363057857  
**Status:** Active

Miniature Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 19.1mm (0.752 Inches), Width of 12.7mm (0.50 Inches), Height of 3.2mm (0.126 Inches), #8 Screw Mounting Method, Bulk Pack

- These miniature mounting bases are ideal for high-density packaging. Threaded insert permits screw to come from outside of mounting surface.

### North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Brand Name	Ty-Rap
Type	2-Way Miniature
Special Features	These miniature mounting bases are ideal for high-density packaging. Threaded insert permits screw to come from outside of mounting surface.
Mount Size	#8
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 Degree F to 185 Degree F

### European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	19.1mm
Width	12.7mm
Height	3.2mm
Suitable for cable tie width to	4.8mm
Type of fastening	Other
Diameter mounting hole	4.4mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

### Packaging

Inner Quantity	1000
Outer Quantity	10000
Outer Dimensions (inches)	17.5x12.75x6.25
Weight Uom	1.25 lbs. per 1000

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: techsupport@tnb.com