



Actual

Catalog Number: CSS-50R
Product ID: 7TAA159100R0005
UPC Number: 78621070069
EAN Number: 05414363149866
Status: Active

Deltec Cable Tie Without Double-Locking Head, Black Acetal for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant, Length of 15.24m (50 Foot) Reel, Width of 12.7mm (0.5 Inches), Thickness of 1.52mm (0.06 Inches), Tensile Strength Rating of 1112 Newtons (250 Pounds), Can Be Cut to Any Desired Length

- Perfect for coaxial, fiber optic and all other communication and electrical conducting cables.
- Strap and body are weatherable acetal, offering superior resistance to sunlight, moisture and salt environments.
- Locking device is marine-grade corrosion-resistant copper alloy.
- Application Tools: WT3D

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Brand Name	Deltec
Type	Strap on a Reel
Special Features	Perfect for coaxial, fiber optic and all other communication and electrical conducting cables.
Application	Ideal solution for bundling in harsh outdoor environments.
Width	.500
Material	Weather Resistant Acetel
Color	Black
Tensile Strength	250 Pounds/1112 Newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	12.7mm
Length belt/tape/tie	15240mm
Tie thickness	1.52mm
Material	Plastic
Material quality	Other
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N

Packaging

Inner Quantity	1
Outer Quantity	10
Outer Dimensions (inches)	8.7x8.35x8.9
Weight Uom	85.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com