



Actual

**Catalog Number:** B14-250F  
**Product ID:** 7TAI029710R0021  
**UPC Number:** 78621080336  
**EAN Number:** 05414363935193  
**Status:** Active

Non-Insulated Female Disconnect Grip, Length .87 Inches, Width .31 Inches, Tab Size .250x.032, Wire Range #16-#14 AWG, Copper, Tin Plated

- Unique construction of the female disconnect offers long-term dependability.
- Brazed seam serrated barrel provides maximum tensile strength.
- Application Tools: WT110M
- Alternate Package Qty: B250G

### North American Specifications (UNSPSC)

UNSPSC	39121447 Wire terminal disconnect
IGCC	4667 Wire terminal disconnect
Brand Name	Sta-Kon
Type	Disconnects
Special Features	Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.
Standard	UL E66716
Material	Brass
Finish	Electro -Tin Plated
Color	Metallic

### European Specifications (ETIM)

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Not Insulated
Material	Copper

### Packaging

Inner Quantity	100
Outer Quantity	500
Outer Dimensions (inches)	10.25x9x7.25
Weight Uom	0.31 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)