

Representative

5333

Catalog Number: Product ID: 7TAD012100R0007 **UPC Number:** 78621005333 **EAN Number:** 05414363075646

Status: Active

3/4 Inch Straight Steel Insulated Liquidtight Connector

- Ability to install quickly with low torque effort
- To positively bond conduit to box or enclosure.

Header	
3D Model	Available on Website

North American Specifications (UNSPSC)		
UNSPSC	39121420 Liquid tight connectors	
IGCC	4585 Liquid tight connectors	
Brand Name	T&B	
Туре	Connectors-Straight	
Application	Used where flexible metal raceway is installed in	
	outdoor or indoor locations where exposed to con-	
	tinuous or intermittent moisture.	
Standard	UL E23018, CSA	
Size	3/4 Inch	
Material	Steel	
Finish	Electro Zinc Plated/Chromate Coating	

<b>European Specifications (ETIM</b>	1)
ETIM	EC001180 Screw connection for protective metallic
	hose
Nominal size in inch	3/4 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to	Thread
housing	
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Steel
Approved in combination with protective	Υ
conduit CSA	
Approved in combination with protective	Υ
conduit UL	

Packaging	
Inner Quantity	25
Inner Dimensions (inches)	8x5x4
Outer Quantity	50
Outer Dimensions (inches)	8.49x5.19x8.13
Weight Uom	23.5 lbs. per 100

<b>Documents / Support Tools</b>	
Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-001535

For further technical assistance, please contact us...



Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com