



Actual

Catalog Number: F2036
Product ID: 7TAI029780R0008
UPC Number: 78621033516
EAN Number: 05414363151128
Status: Active

Polypropylene-Insulated Ferrule, Total Length .748 Inches/19mm, Pin Length .472 Inches/12mm, Pin Diameter .091 Inches/2.3mm, Base Diameter .165 Inches/4.2mm, Wire Range 14 AWG/2.50mm², Color Blue, Copper, Tin Plated

- Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.
- Application Tools: T1, T3, ERG4

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ferrule
Special Features	Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.
Standard	UL E489056
Wire Size	14
Material	Copper
Color	Blue

European Specifications (ETIM)

ETIM	EC000005 Cable end sleeve
Nominal cross section	2.5mm ²
Insulated	Y
Insulation material	Polypropylene
Colour	Blue
Material	Copper
Surface protection	Tinned
Reel packaging	N

Packaging

Inner Quantity	500
Outer Quantity	5000
Outer Dimensions (inches)	8.1x6x3.8
Weight Uom	0.63 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com