



Actual

Catalog Number: 54512
Product ID: 7TAH007500R0012
UPC Number: 78621054512
EAN Number: 05414363074328
Status: Active

Copper Two-Way Splice Connector, Standard Barrel, Max 35kV, Wire Size 4/0 AWG, Tin Plated, Die Code 54, Die Color Code Purple

- Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Color-Keyed
Type	Splice Connector
Special Features	Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.
Material	Copper
Finish	Tin-Plated
Color	Purple
Voltage Rating	600V

Packaging

Inner Quantity	10
Inner Dimensions (inches)	3.3x2.8x2.3
Outer Quantity	100
Outer Dimensions (inches)	12.4x6.4x4
Weight Uom	7.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website
Instruction Sheet 1	ta00676-tb2

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com