



Actual

Catalog Number: L-6-18-9-C
Product ID: 7TAG054030R0005
UPC Number: 72849493367
EAN Number: 05414363028345
Status: Active

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 162mm (6.38 Inches), Width of 2.5mm (0.10 Inches), Thickness of 1.2mm (0.05 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds)

- Application Tools: ERG50, QC-100, L-200, L-400-C

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Brand Name	Catamount
Type	Minature
Standard	UL E49405
Width	0.10 Inches/2.5mm
Length	6.38 Inches/162mm
Thickness	0.05 Inches/1.2mm
Bundle Diameter	0.0625 Inches/1.59mm-1.5 Inches/38.1mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Double Locking Head
Tensile Strength	18 Pounds/80 Newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	2.5mm
Length belt/tape/tie	162mm
Tie thickness	1.2mm
Min. holding force	80N
Model	Internal toothing
Band closure	Double lock head
Material	Plastic
Material quality	Polyamide PA
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N

Packaging

Inner Quantity	100
Inner Dimensions (inches)	12x5x.25
Outer Quantity	20000
Outer Dimensions (inches)	16.7x13.3x10.5
Weight Uom	1.3 lbs. per 1000

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000218

For further technical assistance, please contact us...

Memphis, TN 38125
www.tnb.com

8155 T&B Blvd.
Memphis, TN 38125

Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com