



Actual

**Catalog Number:** L-28-120-0-L  
**Product ID:** 7TAG054410R0013  
**UPC Number:** 72849412576  
**EAN Number:** 05414363128380  
**Status:** Active

Heavy Duty Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 701.32mm (27.611 Inches), Width of 7.62mm (0.30 Inches), Thickness of 1.91mm (0.075 Inches), Tensile Strength Rating of 534 Newtons (120 Pounds)

### North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Brand Name	Catamount
Type	Heavy-Duty
Width	0.30 Inches/7.62mm
Length	27.611 Inches/701.32mm
Thickness	0.075 Inches/1.91mm
Bundle Diameter	0.187 Inches/4.76mm-8.0 Inches/203.2mm
Material	Nylon/Polyamide 6.6 Weather Resistant
Color	Black
Lock Mechanism	Double Locking Head
Tensile Strength	120 Pounds/534 Newtons

### European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	7.62mm
Length belt/tape/tie	701.32mm
Tie thickness	1.91mm
Min. holding force	534N
Model	Internal toothing
Band closure	Double lock head
Material	Plastic
Material quality	Polyamide PA
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N

### Packaging

Inner Quantity	50
Inner Dimensions (inches)	40x6x2
Outer Quantity	500
Outer Dimensions (inches)	39x8x8
Weight Uom	2.5 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289

