



Actual

Catalog Number: L-24-175-0-L
Product ID: 7TAG054520R0002
UPC Number: 72849491280
EAN Number: 05414363078043
Status: Active

Extra Heavy Duty Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 608.22mm (23.946 Inches), Width of 8.76mm (0.345 Inches), Thickness of 2.15mm (0.085 Inches), Tensile Strength Rating of 778 Newtons (175 Pounds)

- Application Tools: L-300C

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Brand Name	Catamount
Type	Extra Heavy-Duty
Standard	UL E49405
Width	0.345 Inches/8.76mm
Length	23.946 Inches/608.22mm
Thickness	0.085 Inches/2.15mm
Bundle Diameter	to 7.2 Inches/182.88mm
Material	Nylon/Polyamide 6.6 Weather Resistant
Color	Black
Lock Mechanism	Double Locking Head
Tensile Strength	175 Pounds/778 Newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	8.76mm
Length belt/tape/tie	608.22mm
Tie thickness	2.15mm
Min. holding force	778N
Model	Internal toothing
Band closure	Double lock head
Material	Plastic
Material quality	Polyamide PA
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N

Packaging

Inner Quantity	50
Inner Dimensions (inches)	18.5x26.75x1.55
Outer Quantity	500
Outer Dimensions (inches)	18.5x26.75x7.9
Weight Uom	2.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000289

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com