



Actual



Family

Catalog Number: KN10-10R-D
Product ID: 7TAI029190R0004
UPC Number: 78621010161
Status: Active

Insulated Nylon Ring Terminal for Wire Range 12-10 Stud Size #10, Yellow

- Molded Funnel Entry Insulator. Brazed Seam. Internal Barrel Serrations.
- Application Tools: WT112M, CM2000A

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Spec-Kon
Type	Ring Terminal
Special Features	Molded Funnel Entry Insulator. Brazed Seam. Internal Barrel Serrations.
Standard	UL E9809
Wire Size	12-10
Voltage Rating	600V
Material	Copper
Color	Yellow

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	PA
Colour insulation	Yellow
Reel packaging	N
AWG-range	12-10

Packaging

Inner Quantity	500
Inner Dimensions (inches)	5.25x4x3.62
Outer Quantity	10000
Outer Dimensions (inches)	5.3x4x3.5
Weight Uom	4.38 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com