



Actual

Catalog Number: RB2577F
Product ID: 7TAI029730R0005
UPC Number: 78621085681
EAN Number: 05414363158592
Status: Active

Nylon Insulated Open Top 90 Degree Flag Female Disconnect Terminal, Length .80 Inches, Width .72 Inches, Maximum Insulation .190, Tab Size .250x.032, Wire Range #16-#14 AWG, Color Blue, Copper, Tin Plated, 500 Pack

- Unique construction of the female disconnect offers long-term dependability.
- Brazed seam serrated barrel provides maximum tensile strength.
- Application Tools: WT145C, WT2000, WT112M, ERG4001
- Alternate Package Qty: RB14250A

North American Specifications (UNSPSC)

UNSPSC	39121447 Wire terminal disconnect
IGCC	4667 Wire terminal disconnect
Brand Name	Sta-Kon
Type	Disconnects
Special Features	Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.
Standard	UL E66716
Material	Brass
Finish	Electro -Tin Plated
Color	Blue
Insulation	Nylon

European Specifications (ETIM)

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Partially Insulated
Colour insulation	Blue
Material insulation	PA
Material	Copper

Packaging

Inner Quantity	500
Inner Dimensions (inches)	6.2x5.2x4.1
Outer Quantity	5000
Outer Dimensions (inches)	13x10.8x10.8
Weight Uom	5 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com