



Actual

Catalog Number: RA18-47PT
Product ID: 7TAI029820R0012
UPC Number: 78621003086
EAN Number: 05414363934226
Status: Active

Nylon Insulated Pin Terminal, Length .85 Inches, Pin Length .390 Inches, Diameter .075 Inches, Wire Range #22-#18 AWG, Color Red, Copper, Tin Plated

- Provides an easy and effective way to terminate stranded wire into European/metric-style terminal blocks.
- Application Tools: WT2000, , ERG4001
- Alternate Package Qty: RA147PT

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Pin Terminals
Special Features	Provides an easy and effective way to terminate stranded wire into European/metric-style terminal blocks.
Standard	UL E9809
Wire Size	22-18
Voltage Rating	300V
Material	Copper
Color	Red

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Pin shape
Insulation	PA
Colour insulation	Red
Reel packaging	N
AWG-range	22-18
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	100
Inner Dimensions (inches)	2.06x1.13x2.94
Outer Quantity	500
Outer Dimensions (inches)	15.2x9.3x8.9
Weight Uom	5 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com