



Actual

Catalog Number: L70
Product ID: 7TAH006720R0037
UPC Number: 78378613002
EAN Number: 05414363129417
Status: Active

Type L - Copper Single Conductor, One-Hole Mount, Socket, Screwdriver Slot Head Screws, Conductor Range 14 Sol-4 Str, Length 1-1/8 Inches, Width 17/32 Inch, Height 35/64 Inch

- Cold forged from pure electrolytic copper with 99 percent conductivity.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Copper Connectors
Special Features	Cold forged from pure electrolytic copper with 99 percent conductivity.
Standard	UL E9809
Material	Copper
Conductor Range (Main/Primary)	14 Sol.-4 Str.

Packaging

Inner Quantity	100
Inner Dimensions (inches)	4x3x2.6
Outer Quantity	1000
Outer Dimensions (inches)	15.1x6.8x5
Weight Uom	3.31 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com