



Actual

**Catalog Number:** RAS18-250AX  
**Product ID:** 7TAI029830R0097  
**UPC Number:** 78621007075  
**EAN Number:** 05415022254853  
**Status:** Active

Heat Shrinkable Fully Insulated Female Disconnect Terminal, Length 1.82 Inches, Maximum Insulation .170, Tab Size .250x.032, Wire Range #22-#18 AWG, Color Red, Copper, Tin Plated

- Unique construction of the female disconnect offers long-term dependability.
- Brazed seam serrated barrel provides maximum tensile strength.
- Application Tools: WT1255

### North American Specifications (UNSPSC)

UNSPSC	39121447 Wire terminal disconnect
IGCC	4667 Wire terminal disconnect
Brand Name	Sta-Kon
Type	Disconnects
Special Features	Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.
Material	Brass
Finish	Electro -Tin Plated
Color	Red

### European Specifications (ETIM)

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Fully Insulated
Colour insulation	Red
Material	Copper

### Packaging

Inner Quantity	25
Inner Dimensions (inches)	2.5x1.3x3.5
Outer Quantity	250
Outer Dimensions (inches)	16.4x6.9x4.5
Weight Uom	6.25 lbs. per 1000

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)