


**Catalog Number:** 2RCS10X  
**Product ID:** 7TAI029900R0001  
**UPC Number:** 78621070328  
**EAN Number:** 05414363140634  
**Status:** Active



Heat Shrinkable Butt Splice, Length 1.60 Inches, Width .31 Inches, Maximum Insulation Diameter .250, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated

- Self-insulated with heat-shrinkable polyolefin and internally coated sealant. Upon completed installation, a fully sealed connection is achieved to protect the joint against the degrading effects of galvanic action, corrosion, and environmental exposure.
- Application Tools: WT1255
- Alternate Package Qty: RCCS22X

Actual

### North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Sta-Kon
Type	Splice Connector
Special Features	Self-insulated with heat-shrinkable polyolefin and internally coated sealant. Upon completed installation, a fully sealed connection is achieved to protect the joint against the degrading effects of galvanic action, corrosion, and environmental exposure.
Material	Copper
Finish	Electro -Tin Plated
Color	Yellow
Voltage Rating	600V
Temperature Rating	150 Degrees C

### Packaging

Inner Quantity	25
Outer Quantity	125
Outer Dimensions (inches)	15x9.5x8.8
Weight Uom	8.75 lbs. per 1000

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)