

Catalog Number: TV14-250PD-XV
Product ID: 7TAI029350R0278
UPC Number: 72849414473
EAN Number: 05414363489368
Status: Active



Insulated Vinyl Piggy Back - 250 Series Disconnects for Wire Range 16-14, Blue, Canister

- Male and Female Tabs Combined. Additional conductors may be added to existing installations without changing blocks. Molded Insulator. Brazed Seam. Internal Barrel Serrations. Funnel Entry.
- Application Tools: WT112M, CM2000A
- Alternate Package Qty: TV14250PDL

Actual



Family

North American Specifications (UNSPSC)

UNSPSC	39121447 Wire terminal disconnect
IGCC	4667 Wire terminal disconnect
Brand Name	Catamount
Type	Disconnects
Special Features	Male and Female Tabs Combined. Additional conductors may be added to existing installations without changing blocks. Molded Insulator. Brazed Seam. Internal Barrel Serrations. Funnel Entry.
Standard	UL E66716
Material	Brass with Copper Sleeve
Color	Blue
Insulation	Vinyl

European Specifications (ETIM)

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Partially Insulated
Colour insulation	Blue
Material insulation	PVC

Packaging

Inner Quantity	75
Inner Dimensions (inches)	6x4.5x4
Outer Quantity	900
Outer Dimensions (inches)	11x10x8
Weight Uom	5 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com