



Representative

Catalog Number: 5264
Product ID: 7TAD012070R0002
UPC Number: 78621005264
EAN Number: 05414363075530
Status: Active

Liquidtight Sealing Gasket, 1 Inch, with 316 Stainless Steel Retainer and Santoprene Sealing Material

- Design locks resilient sealing material in stainless steel.
- Stainless steel retainer protects seal from extruding out under torque and limits compression to an optimum predetermined value; provides high quality seal.
- Resilient material flows and seals rough edges.

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	T&B
Type	Sealing Gaskets
Application	When used with an externally threaded connector provides a tight seal against oil, fumes or moisture at the knockout opening.
Standard	UL E13938, CSA
Size	1 Inch
Material	Stainless Steel

European Specifications (ETIM)

ETIM	EC001181 Sealing ring
Model	O-ring
Material	Other
Fitting for thread size NPT	1

Packaging

Inner Quantity	25
Inner Dimensions (inches)	3.5x3x3
Outer Quantity	50
Outer Dimensions (inches)	6.5x3.75x3.13
Weight Uom	1.81 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-001558

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com