



Actual

**Catalog Number:** 15005-001  
**Product ID:** 7TAD012810R0000  
**UPC Number:** 03448123304  
**Status:** Active

1/2 Inch Gray Liquidtight Flexible Non-metallic Conduit, 1,000 Foot Reel

- Lightweight for easy handling, transportation and installation.
- Crush, abrasion and strain resistant.
- Provides superior wire protection
- Smooth interior ideal for pulling cable, no jagged edges.
- Maintains internal I.D. even in tight radius bends.
- Air conditioning and heating
- Computer power distribution
- Machine Tools
- Console wiring
- Transformer connections
- Outdoor lighting

### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	Carlton
Type	Liquidtight Flexible Non-Metallic Conduit & Fittings
Special Features	Non-Conductive and Non-Corrosive.
Application	Control and Motor
Standard	cULus E95745
Trade Size	1/2 Inch
Length	1,000 Feet
Material	PVC
Color	Gray

### European Specifications (ETIM)

ETIM	EC001175 Corrugated plastic hose
Nominal size in inch	1/2 inch
Material	PVC
Oil resistant	Y
Colour	Grey
Lengthwise slotted	N
Closable (two-part)	N
Approved according to UR	Y

### Packaging

Outer Quantity	1000
Outer Dimensions (inches)	36x36x14
Weight Uom	0.17 lbs. Each

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-ac03996

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)