



Other

Catalog Number: HS-KIT
Product ID: 7TAA017300R0306
UPC Number: 78621093898
EAN Number: 05415022255584
Status: Active

Thin-Wall Heat Shrinkable Tubing Assortment Precut in 6 Inch Lengths, Black, (32)-Diameter 3/16 Inch, (20)-Diameter 1/4 Inch, (8)-Diameter 3/8 Inch, (6)-Diameter 1/2 Inch, (4)-Diameter - 3/4 Inch, (4)-Diameter - 1 Inch Includes Plastic Storage Case

- Flame-retardant, cross-linked polyolefin.
- Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C; MIL-DTL-23053/5 Class 1&2; AMS 3636 & 3637; DEF STAN 59-97, Issue 3, Type 2a

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Brand Name	Shrink-Kon
Shrink Ratio	3:1
Length	6.0 Inches/152.4mm
Minimum Shrink Temperature	248 Degrees F (120 C)
Color	Black

Packaging

Outer Quantity	1
Outer Dimensions (inches)	1.938x10.813x6.75
Weight Uom	129.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com