



Actual



Representative

Catalog Number: 146-TB
Product ID: 7TAD012050R0008
UPC Number: 78621000146
EAN Number: 05414363076704
Status: Active

2 Inch Steel Locknut for Use With Rigid/IMC Conduit

- Tightens without deformation
- To effectively bond conduit or connector to box or enclosure.

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	31161716 Locknuts
IGCC	2849 Locknuts
Brand Name	T&B
Type	Locknuts
Special Features	Hardened Steel, Malleable Iron, Copper-Free Aluminum Construction
Application	To Connect Externally Threaded Conduit or Connector to a Threadless Opening In a Box or Enclosure.
Standard	UL E23018, CSA
Material of Construction	Steel
Thread Size	2 Inch

European Specifications (ETIM)

ETIM	EC002382 Locknut
Material	Steel
Surface protection	Untreated
With nylon ring	N

Packaging

Inner Quantity	25
Inner Dimensions (inches)	4x4.5x6
Outer Quantity	50
Outer Dimensions (inches)	9x5.25x7.25
Weight Uom	11 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com