



Actual



Family

Catalog Number: CC-NPT-12-G
Product ID: 7TAD105060R0005
UPC Number: 78621007824
EAN Number: 05415022189667
Status: Active
Replacement Catalog: CC-NPT-12-B

Cable Gland with NPT Threads, NPT Thread Size 1/2 Inch, Cord Range 0.394 Inch/10mm to 0.551 Inch/14mm, Thread Length 0.590 Inch/15mm, IP68 Rating, Halogen Free, Nylon, Gray

- Sturdy cable sealing mechanism which results in superior strain relief.
- Compact size ensures quick and easy installation in cramped spaces
- Non-metallic construction provides excellent corrosion, chemical and impact resistance.

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Cable Glands
Special Features	Sturdy Cable Sealing Mechanism Which Results In Superior Strain Relief
Application	Ideal for Connections and Strain Relief in Cramped Spaces
Standard	UL E13938, CSA
Size	1/2 Inch
Conductor Range	0.394 Inch/10mm to 0.551 Inch/14mm
Material	Nylon
Color	Gray
NEMA Rating	NEMA 4
Temperature Rating	-30 to +80 Degrees C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Thread length	15.0mm
Suitable for cable diameter	10.0-14.0mm
Material	Plastic
Material quality	Polyamide (PA)
Degree of protection (IP)	IP68
Colour	Light grey
Model	Straight
Operating temperature	-30-+80°C

Packaging

Inner Quantity	50
Inner Dimensions (inches)	4x4x3
Outer Quantity	250
Outer Dimensions (inches)	20.4x5.5x8.8
Weight Uom	3.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000004

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com