



Representative

Catalog Number: 35301G
Product ID: 7TAH006040R0108
UPC Number: 78621081899
Status: Active

Locktite One-Hole Lug, Offset Tongue, Copper Tongue, Conductor Range 14-6 AWG, #10 Bolt, Green Screw for Grounding Identification, Steel Cadmium Plated

- Double laps at top give greater thread strength and lock screw when tightened.
- Copper tongue makes a low resistance terminal.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Locktite Connectors
Special Features	Double laps at top give greater thread strength and lock screw when tightened.
Standard	UL E9809, CSA 4503, CSA 7222
Material	Copper
Finish	Steel Cadmium Plated
Conductor Range (Main/Primary)	14-6
Number Of Mounting Holes	1
Mounting Hole Spacing	7/32 Inch
Bolt Size	#10

Packaging

Inner Quantity	100
Inner Dimensions (inches)	3.5x3x3
Outer Quantity	500
Outer Dimensions (inches)	16.3x4.2x3.9
Weight Uom	2.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com