



Actual

**Catalog Number:** **LT43F-NEW**  
**Product ID:** 7TAD012890R0008  
**UPC Number:** 03448119418  
**EAN Number:** 05415022248401  
**Status:** Active

1 Inch, Straight, Two-Piece Liquidtight Non-Metallic Fitting, UL E32447, Temperatures up to 107 Degrees C, Nitril Rubber O-Ring, PVC, Grey

- Non-conductive and non-corrosive.
- Resistant to oil, acid, ozone and alkaline.
- Easy to install.
- Approved for indoor and outdoor locations
- UL listed for wet locations
- Nitrile rubber &apos;O&apos; ring for a liquidtight termination.
- Temperatures up to 225 degree F (107 degree C)
- Meets UL standard 514B.

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	Carlon
Type	Liquidtight Fittings
Application	For use with Carflex conduit and Carflex X-Flex conduit.
Standard	cULus
Size	1 Inch
Material	Non-Metallic

### European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	1 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
Thread length	17.78mm
One-piece	N
Material screw gland	Other
Colour	Grey

### Packaging

Outer Quantity	25
Outer Dimensions (inches)	11.5x7.7x5.7
Weight Uom	0.16 lbs. Each

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-ac04398

**For further technical assistance, please contact us...**

8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)