



Actual



Representative

Catalog Number: 2520-2
Product ID: 7TBD105010R0000
UPC Number: 78621058293
EAN Number: 05415022258141
Status: Active

Multi-Hole Cord Connector with 2 Holes, Hub Size 1/2 Inch, Cord Diameter 0.210 to .230 Inch, Steel

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Multi-Hole Cord Connectors
Application	Ideal for Environments Where there is a Need to Run Multiple Cables Into an Enclosure and Space At The Enclosure is Limited.
Size	1/2 Inch
Conductor Range	0.210 to 0.230 Inch
Material	Steel
Color	Metallic
Temperature Rating	105 Degrees C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Thread length	15.875mm
Suitable for cable diameter	5.33-5.84mm
Material	Metal
Material quality	Steel
Colour	Natural colour
Model	Straight

Packaging

Inner Quantity	25
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	100
Outer Dimensions (inches)	10.9x10.1x3.9
Weight Uom	15.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com