









6, 10, 16, 24, 32, 48 Contacts + Ground

24	32	48
		

Install to
Matching Series
Hood/Base

Screw Terminal Inserts		24 + G	32 + G	48 + G
	Male Pins 20-14 AWG (0.5-2.5 mm ²)	MS224B	MS216B (1-16) +MS232B (17-32)	MS224B (1-24) +MS248B (25-48)
	Female Sleeves 20-14 AWG (0.5-2.5 mm ²)	FS124B	FS116B (1-16)+ FS132B (17-32)	FS124B (1-24)+ FS148B (25-48)

Screw Terminal Wiring Adapter Blocks		24 + G
	Male Insert, Ground L. 20-14 AWG (0.5-2.5 mm ²)	MS224WAL
	Male Insert, Ground R. 20-14 AWG (0.5-2.5 mm ²)	MS224WAR
	Female Insert, Ground L. 20-14 AWG (0.5-2.5 mm ²)	FS124WAL
	Female Insert, Ground R. 20-14 AWG (0.5-2.5 mm ²)	FS124WAR
	Foot Element mounting adapter for DIN rail	FE807TB



Wiring Adapter Insert for use with Panel Bases; allows single access direction panel-build wiring + easy terminal ID for service & testing.

Accessories:	Catalog No.
Label Insert Clip	WAM-1
Strip blank	WAM1B
Strip Nos. 1-64	WAM1N64
Strip Letters A - Z	WAM1AZ


Pos-E-Kon™




Use small blade screwdriver to push wire entry tab in for EZ contact removal.

Crimp Terminal Inserts		24 + G	32 + G	48 + G
	Male Insert (Order contacts below)	MC424B	(1-16) MC416B (17-32) MC432B	(1-24) MC424B (25-48) MC448B
	Female Insert (Order contacts below)	FC324B	(1-16) FC316B (17-32) FC332B	(1-24) FC324B (25-48) FC348B



Contacts Selection			For all Crimp Terminal "B" Inserts	
Crimp Contacts	Wire Gauge AWG (mm ²)	Identification	Female	Male
	20 AWG (0.5 mm ²)	No Groove	FP2000	MP2000
	18 AWG (0.75-1 mm ²)	1 Groove	FP1800	MP1800
	16 AWG (1.5 mm ²)	2 Grooves	FP1600	MP1600
	14 AWG (2.5 mm ²)	3 Grooves	FP1400	MP1400
	12 AWG (4.0 mm ²)	No Groove	FP1200	MP1200

Allows use of "open" interiors as separable barrier terminal blocks for panel assemblies; or can be used as OEM wiring assembly fixture.

DIN Rail Adapter Mount Frames		24 + G
	150 mm long, with base for snapping onto 33 mm rail	AMF124