



Actual

**Catalog Number:** TYD-50R  
**Product ID:** 7TAA159090R0005  
**UPC Number:** 78621071340  
**EAN Number:** 05414363067245  
**Status:** Active

Deltec Cable Tie Without Double-Locking Head, Black Acetal for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant, Length of 15.24m (50 Foot) Reel, Width of 12.7mm (0.5 Inch), Thickness of 1.52mm (0.06 Inch), Tensile Strength Rating of 1112 Newtons (250 Pounds), Can Be Cut to Any Desired Length

- Perfect for coaxial, fiber optic and all other communication and electrical conducting cables.
- Strap and body are weatherable acetal, offering superior resistance to sunlight, moisture and salt environments.
- Locking device is marine-grade corrosion-resistant copper alloy.
- Application Tools: WT3D

### North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Brand Name	Deltec
Type	Strap on a Reel
Special Features	Perfect for coaxial, fiber optic and all other communication and electrical conducting cables.
Application	Ideal solution for bundling in harsh outdoor environments.
Width	0.5 Inch/12.7mm
Material	Weather Resistant Acetel
Color	Black
Tensile Strength	250 Pounds/1112 Newtons

### European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	12.7mm
Length belt/tape/tie	15240mm
Tie thickness	1.52mm
Min. holding force	1112N
Operating temperature	-40-+85°C
Model	Internal toothing
Band closure	Double lock head
Material	Plastic
Material quality	Polyoxymethylene (POM)
Surface protection	Untreated
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
Type of fastening	None
MIL approval	N
UL approval	N

### Packaging

Inner Quantity	1
Outer Quantity	5

Outer Dimensions (inches)	9.4x9.2x4.5
Weight Uom	97 lbs. per 100

## Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com