



Actual

Catalog Number: TC111A
Product ID: 7TAA116060R0000
UPC Number: 78599102495
EAN Number: 05415022254143
Status: Active

Compression Connector, Concrete Tight, Concrete Tight, Conduit Size 1/2 Inch, Material Steel, For use with EMT Conduit

- Concrete Tight
- Zinc plated

North American Specifications (UNSPSC)

UNSPSC	39121434 Electrical metallic tubing EMT connectors
IGCC	4611 Electrical metallic tubing EMT connectors
Brand Name	Steel City
Type	EMT Conduit Fittings
Special Features	Concrete Tight
Application	For use with EMT conduit
Standard	UL E16592
Material	Steel
Finish	Zinc Plated

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
One-piece	Y
Material housing	Steel
Surface protection	Untreated
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit FI	N

Packaging

Inner Quantity	50
Inner Dimensions (inches)	6.25x4.75x3.25
Outer Quantity	500
Outer Dimensions (inches)	17.7x10.2x6.3
Weight Uom	11 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com