

**Catalog Number:** TV14-250PD-L  
**Product ID:** 7TAI029350R0277  
**UPC Number:** 78620993769  
**EAN Number:** 05414363603047  
**Status:** Active



Insulated Vinyl Piggy Back - 250 Series Disconnects for Wire Range 16-14 , Blue

- Male and Female Tabs Combined. Additional conductors may be added to existing installations without changing blocks. Molded Insulator. Brazed Seam. Internal Barrel Serrations. Funnel Entry.
- Application Tools: WT112M, CM2000A

### North American Specifications (UNSPSC)

UNSPSC	39121447 Wire terminal disconnect
IGCC	4667 Wire terminal disconnect
Brand Name	Catamount
Type	Disconnects
Special Features	Male and Female Tabs Combined. Additional conductors may be added to existing installations without changing blocks. Molded Insulator. Brazed Seam. Internal Barrel Serrations. Funnel Entry.
Standard	UL E9809
Material	Brass with Copper Sleeve
Color	Blue
Insulation	Vinyl

### European Specifications (ETIM)

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Partially Insulated
Colour insulation	Blue
Material insulation	PVC

### Packaging

Inner Quantity	50
Inner Dimensions (inches)	7x4x.01
Outer Quantity	500
Outer Dimensions (inches)	11x8x18
Weight Uom	2.5 lbs. per 1000

### Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

Actual



Family

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)