



Actual

**Catalog Number:** E6-10  
**Product ID:** 7TAI029580R0025  
**UPC Number:** 78621080357  
**EAN Number:** 05414363150497  
**Status:** Active

Non-Insulated Large Brazed Seam Ring Terminal, Length 1.13 Inches, Width .48 Inches, Bolt Hole #10, Wire Range #6 AWG, Copper, Tin Plated, 20 Pack

- These non-insulated ring terminals are made of electrolytic copper for high conductivity.
- They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
- Serrated barrel increases grip on wire.
- Application Tools: WT115A, TBM6, TBM6S, WT3185
- Alternate Package Qty: E26

## North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ring Terminal
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.
Standard	UL E9809
Wire Size	6
Voltage Rating	600V
Material	Copper
Color	Metallic

## European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	N
Material	Copper
Surface protection	Tinned

## Packaging

Inner Quantity	20
Inner Dimensions (inches)	2.09x1.1x2.9
Outer Quantity	100
Outer Dimensions (inches)	10.5x9x7
Weight Uom	1.63 lbs. per 100

## Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.

T&B Technical Support  
MS 3B-50

Hours: 7AM - 6PM CDT  
Monday-Friday

Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

8155 T&B Blvd.  
Memphis, TN 38125

Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)