



Representative

Catalog Number: PB132
Product ID: 7TAA080300R0010
UPC Number: 78621079125
EAN Number: 05415022426052
Status: Active

Double lever locking panel base for use with B32, C12, D80 and DD144 series.

North American Specifications (UNSPSC)

UNSPSC	39121424 Terminal block covers
IGCC	4594 Terminal block covers
Brand Name	Pos-E-Kon
Application	For use with B32, C12, D80 and DD144 series
Material	Die-Cast Aluminum Alloy
Finish	Epoxy Powder Coated
Voltage Rating	600 VAC
Temperature Rating	-40 Degrees F to +257 Degrees F

European Specifications (ETIM)

ETIM	EC000437 Housing for industrial connectors
Shape	Rectangular
Length	124.2568mm
Height	29.9974mm
Width	79.2734mm
Type of housing	Other
Position cable feed	Sideways
With cable screw gland	N
With hinged lid	N
Material housing	Aluminium
Coating housing	With powder coating
Locking mechanism	Double locking levers
Inflammability class of insulation material acc. with UL94	V0
Operation temperature	-40 - +125°C

Packaging

Outer Quantity	10
Outer Dimensions (inches)	12.3x6.7x4.7
Weight Uom	49.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-001245

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com