



Representative



Family

Catalog Number: CC-ISO20-G
Product ID: 7TAD105080R0011
UPC Number: 78621021173
EAN Number: 05414363149279
Status: Active

Cable Gland with ISO/Metric Threads, ISO Thread Size 20mm, Cord Range 0.236 Inch/6mm to 0.473 Inch/12mm, Thread Length 0.590 Inch/15mm, IP68 Rating, Halogen Free, Nylon, Gray

- Sturdy cable sealing mechanism which results in superior strain relief.
- Compact size ensures quick and easy installation in cramped spaces
- Non-metallic construction provides excellent corrosion, chemical and impact resistance.

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Cable Glands
Special Features	Sturdy Cable Sealing Mechanism Which Results In Superior Strain Relief
Application	Ideal for Connections and Strain Relief in Cramped Spaces
Standard	CSA
Size	ISO 20
Conductor Range	0.236 Inch/6mm to 0.473 Inch/12mm
Material	Nylon
Color	Gray
NEMA Rating	NEMA 4
Temperature Rating	-30 to +80 Degrees C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	Metric
Nominal thread size metric/PG	20
Thread length	15.0mm
Suitable for cable diameter	6.0-12.0mm
Material	Plastic
Material quality	Polyamide (PA)
Degree of protection (IP)	IP68
Colour	Light grey
Model	Straight
Operating temperature	-30-+80°C

Packaging

Inner Quantity	50
Inner Dimensions (inches)	8x5x4
Outer Quantity	200
Outer Dimensions (inches)	16.7x10.5x4.5
Weight Uom	3.19 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000004

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com