



Actual

Catalog Number: 13713B
Product ID: 7TAA131850R0047
UPC Number: 78621070171
EAN Number: 05414363111474
Status: Active

Die for 14 Ton 13100A or 15 Ton TBM15i Hydraulic Tool for Crimping 2200 Series Dragon Tooth Terminals

- Application Tools: 13100A, TBM15I

North American Specifications (UNSPSC)

UNSPSC	27112820 Lug crimping tool dies
IGCC	2427 Lug crimping tool dies
Brand Name	Dragon Tooth
Type	Die
Application	Crimping Dragon Tooth terminal for magnet wire
Material	Alloy Steel
Color	Silver

European Specifications (ETIM)

ETIM	EC001282 Insert for crimp tool cable lugs, cable end sleeves, screen connection
Application	Insulated varnish wire-cable lugs and connectors
Cross section	50,000 - 230,000mm ²
AWG-range	10 - 1/0
Compression shape	Trapezoid compression

Packaging

Outer Quantity	1
Outer Dimensions (inches)	4x4x3
Weight Uom	100 lbs. per 100

Documents / Support Tools

Instruction Sheet 1	ta02760-tb2
---------------------	-------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com